



Gas Analysis

Sample Gas Coalescing Filter K-AGF-VA-23

Gas analysis is a complex field. The sample gas to be analysed must be extracted and handled under quite diverse conditions to yield representative and reliable analysis results. One disturbance variable which must also be eliminated is aerosols.

The aqueous suspended particles can easily be removed from the gas by coagulation using special filter matrices. During this process, the tiny aerosols accumulate on the fibres of the filter matrix through collision, forming drops increasing in size. Once large enough, the condensate which forms drains into the filter bowl and is then removed.

Model K-AGF-VA-23 has the housing from the AGF-VA filter series made from stainless steel and with the respective fittings to adapt it for the coagulation function.

The easy installation and the Unique quick-release fastener are additional features of this model.

Bühler Unique quick-release fastener

Very quick and easy filter changes without tools

Low dead volume


Variable wall-mounting via spacer block

Condensate drain through connection thread (G3/8) inside the filter cover

Bypass connection inside the filter head (G1/4)



Dimensions





Use in explosive areas (additional notices):

The filter meets the fundamental safety requirements of Directive 2014/34/EU and is suitable for use in Category 2G, Explosion class IIC areas. The filter is not marked, as it does not have an innate ignition source and Directive 2014/34/EU therefore does not apply.

Flammable gases, explosion class IIB or IIC, which could occasionally be explosive during normal operation may be conveyed through the filter.

Be sure to observe the instructions in the respective operating instructions!

Ambient temperature range when used in Ex areas: -5 °C \leq T_{amb} \leq 60 °C.

Technical Data

K-AGF-VA-23 Coalescence Filter

Dead volume with filter element	55 ml		
Material - filter housing	1.4571 / SS 316 Ti		
Material - gasket	available in Viton or perfluorelastomer		
Material - filter element	see table		
Weight	1.7 kg		
Operating pressure max.	160 bar		
Medium temperature max.	140 °C		

Ordering instructions

The filter includes a spacer block, 2 fixing bolts DN 912 M5 x 80, as well as sealing plugs inside the bypass and condensate out connection.

Filter*

Item no.	Model	Seal
41 42 799	K-AGF-VA-23-V	Viton
41 42 899	K-AGF-VA-23-P	Perfluorelastomer

^{*} one filter element is included with delivery.

Filter element

Item no.	Model	Filter element	Material	Filter surface	Packing unit	Ex application
49 32 001	12-57-C	Sleeve	Borosilicate fibre	28 cm ²	1 pieces	IIC